



YAZV262NT38FX, Compression Terminal, 2/0 Flex G,H,I,K,M, DLO, 2/0 AWG Cu, 2- Hole, 3/8" Stud, Long Barrel

By Burndy

Catalog # [YAZV262NT38FX](#)

Copper Compression Terminal

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Range	
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Flex I Size	2/0 AWG
Range	
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper DLO Size	2/0 AWG
Range	
Conductor - Copper Str	"2/0 AWG"
Compact Size	
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex G Size	2/0 AWG
Range	
Conductor - Copper Str Navy	125
Size	
Conductor Type	CODE/FLEX



Conductor - Copper Str Size	2/0 AWG
Range	
Conductor - Copper Flex H Size	2/0 AWG
Range	
Conductor - Copper Flex I Size	"2/0 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Stud Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Size inch	0.38

General

Trade Name	HYLUG™
Die Index	13
Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Y
Color Code	Black
UPC	781810669457
Type	Long Barrel, Skive
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810669457
UPC 14 Digit GTIN	00781810669457

Logistics

Minimum Pack Quantity	100
Pallet Quantity	19600

Carton Quantity50

Product Assets

[Catalog \[English\]](#)



A Hubbell brand