



**YAZV26TC12FX, Cu Compression, 1-Hole,
1/2" Stud, Long Barrel, 2/0 Flex G, H, I, M,
DLO, 2/0 AWG**

By Burndy
Catalog # [YAZV26TC12FX](#)

2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, CU, 1 Hole, 1/2 Stud, Long
Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2/0 AWG
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex M Size Range	2/0 AWG
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper Str Compact Size	"2/0 AWG"
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex G Size Range	2/0 AWG



Conductor - Copper Str Navy Size	125
Conductor - CopperWeld Str Size Range	2/0 F AWG-2/0 V AWG
Conductor - CopperWeld Str Size	• 2/0 F AWG • 2/0 G AWG • 2/0 J AWG • 2/0 K AWG • 2/0 V AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	"2/0 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.93 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	77 mm
Dimension - Outside Diameter inch	0.63 in
Dimension - Hole Size mm	13.5 mm
Dimension - Hole Size inch	0.53
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2

Physical Attribute - Tongue Angle	Straight	UPC	781810241585
Dimension - B Length fraction	1-1/2 in	Type	Long Barrel, Skive
Dimension - Z inch	0.55 in	Material	Copper
Dimension - B Length inch	1.50 in	Plating Type	Tin
Dimension - N inch	0.53 in	Finish Type	Tin-Plated
Dimension - Bolt Size inch	0.5	UPC 12 Digit	781810241585
Dimension - Length Overall inch	3.05 in	UPC 14 Digit GTIN	00781810241585
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	13	Carton Quantity	20
Feature - Barrel Type	Long	Product Assets	
Feature - Barrel Style	Skived	Catalog [English]	
Plated	Y	Installation Manual [English]	
Color Code	Black	Installation Manual [French, English]	



A Hubbell brand