



YAZV26TC12FXB, Compression Terminal, 2/0 Flex G,H,I,K,M, DLO, 2/0 AWG Cu, 1- Hole, 1/2" Stud, Long Barrel

By Burndy
Catalog # [YAZV26TC12FXB](#)

Copper Compression Terminal

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2/0 AWG
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex M Size Range	2/0 AWG
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper Str Compact Size	"2/0 AWG"
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex G Size	2/0 AWG



Conductor - Copper Str Navy Size	125
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	"2/0 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.93 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	81 mm
Dimension - Outside Diameter inch	0.63 in
Dimension - Thread Size	1/2
Dimension - Hole Size mm	13.5 mm
Dimension - Hole Size inch	0.53
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-5/8 in
Dimension - Z inch	0.55 in
Dimension - B Length inch	1.63 in
Dimension - D inch	1.08 in
Dimension - N inch	0.53 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	3.18 in

General

Trade Name	HYLUG™
Die Index	13
Feature - Barrel Type	Long
Feature - Barrel Style	- Belled - Skived
Plated	Y
Color Code	Black
UPC	781810431313
Type	Long Barrel, Skive
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated

UPC 12 Digit	781810431313
UPC 14 Digit GTIN	00781810431313

Logistics

Minimum Pack Quantity	1
Pallet Quantity	17400
Carton Quantity	50

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand