



YAZV28NT38FX, Compression Terminal, 4/0 Flex G, H, I, K, M, DLO, 4/0 AWG Cu, 1-Hole, 3/8" Stud, Long Barrel, Narrow Tongue

By Burndy

Catalog # [YAZV28NT38FX](#)

4/0 Flex G,H,I,K,M,DLO, 4/0 AWG, CU, 1 Hole, 3/8 Stud, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	4/0 AWG
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor - Copper Flex K Size	"4/0 AWG"
Conductor - Copper Flex M Size	"4/0 AWG"
Conductor - Copper Str Size	"4/0 AWG"
Conductor - Copper Flex I Size Range	4/0 AWG
Conductor - Copper Flex G Size	"4/0 AWG"
Conductor - Copper DLO Size Range	4/0 AWG
Conductor - Copper Str Compact Size	"4/0 AWG"
Conductor - Copper DLO Size	4/0 AWG
Conductor Size	4/0 AWG
Conductor - Copper Flex H Size	"4/0 AWG"
Conductor - Copper Flex G Size Range	4/0 AWG



Conductor - Copper Str Navy Size	200
Conductor - CopperWeld Str Size	• 4/0 E • 4/0 EK • 4/0 F • 4/0 G • 4/0 V
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size	"4/0 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.94 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	76 mm
Dimension - Outside Diameter inch	0.77 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight

Dimension - B Length fraction	1-5/8 in
Dimension - Z inch	0.42 in
Dimension - B Length inch	1.62 in
Dimension - N inch	0.41 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	3.01 in

General

Trade Name	HYLUG™
Die Index	15
Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Y
Color Code	Purple

UPC	781810241646
Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 14 Digit GTIN	00781810241646

Logistics

Minimum Pack Quantity	10
Pallet Quantity	14500
Carton Quantity	50

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand