



YAZV28TC12FX, Compression Terminal, 4/0 Flex G,H,I,K,M, DLO, 4/0 AWG Cu, 1- Hole, 1/2" Stud, Long Barrel

By Burndy

Catalog # [YAZV28TC12FX](#)

4/0 Flex G,H,I,K,M,DLO, 4/0 AWG, CU, 1 Hole, 1/2 Stud, Long
Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Range	
Conductor - Copper Flex K Size	"4/0 AWG"
Conductor - Copper Flex M Size	4/0 AWG
Range	
Conductor - Copper Flex M Size	"4/0 AWG"
Conductor - Copper Str Size	"4/0 AWG"
Conductor - Copper Flex I Size	4/0 AWG
Range	
Conductor - Copper Flex G Size	"4/0 AWG"
Conductor - Copper DLO Size	4/0 AWG
Range	
Conductor - Copper Str	"4/0 AWG"
Compact Size	
Conductor - Copper DLO Size	4/0 AWG
Conductor Size	4/0 AWG



Conductor - Copper Flex H Size	"4/0 AWG"
Conductor - Copper Flex G Size	4/0 AWG
Range	
Conductor - Copper Str Navy	200
Size	
Conductor - CopperWeld Str	4/0 E AWG-4/0 V AWG
Size Range	
Conductor - CopperWeld Str	• 4/0 E AWG • 4/0 EK AWG • 4/0 F AWG • 4/0 G AWG • 4/0 V AWG
Size	
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	4/0 AWG
Range	
Conductor - Copper Flex H Size	4/0 AWG
Range	
Conductor - Copper Flex I Size	"4/0 AWG"

Configuration

Physical Attribute - Number of	1
Holes	
Number of Pad Holes	1
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.14 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	83 mm
mm	
Dimension - Outside Diameter	0.77 in
inch	
Dimension - Hole Size mm	13.5 mm
Dimension - Hole Size inch	0.53
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2

Dimension - Bolt Hole Size inch	0.52 in	Sub Brand	HYLUG
Dimension - Bolt Size fraction	1/2	UPC	781810241707
Physical Attribute - Tongue Angle	Straight	Type	Long Barrel, Skive
Dimension - B Length fraction	1-5/8 in	Material	Copper
Dimension - Z inch	0.55 in	Plating Type	Tin
Dimension - B Length inch	1.62 in	Finish Type	Tin-Plated
Dimension - N inch	0.53 in	UPC 12 Digit	781810241707
Dimension - Bolt Size inch	0.5	UPC 14 Digit GTIN	00781810241707
Dimension - Length Overall inch	3.26 in		
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	15	Pallet Quantity	11600
Feature - Barrel Type	Long	Carton Quantity	25
Feature - Barrel Style	Skived		
Plated	Y	Product Assets	
Color Code	Purple	Catalog [English]	
		Installation Manual [English]	
		Installation Manual [French, English]	



A Hubbell brand