



YAZV292NT516FX, Compression Terminal, 250 kcmil, 4/0 G, H, I, K, M, DLO, Cu, 2-Hole, 5/16" Stud, 1-3/4" Spacing, Long Barrel, Narrow Tongue

By Burndy

Catalog # [YAZV292NT516FX](#)

250 kcmil, 4/0 G,H,I,K,M,DLO, CU, 2 Hole, 5/16 Stud, 1-3/4 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	250 KCMIL
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor - Copper Flex K Size	"4/0 AWG"
Conductor - Copper Flex M Size	"4/0 AWG"
Conductor - Copper Str Size	"4/0 AWG"
Conductor - Copper Flex I Size Range	4/0 AWG
Conductor - Copper Flex G Size	"4/0 AWG"
Conductor - Copper DLO Size Range	4/0 AWG
Conductor - Copper Str Compact Size	"4/0 AWG"
Conductor - Copper DLO Size	4/0 AWG
Conductor Size	250 KCMIL
Conductor - Copper Flex H Size	"4/0 AWG"
Conductor - Copper Flex G Size Range	4/0 AWG



Conductor - Copper Str Navy Size	200
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	250 kcmil
Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size	"4/0 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.96 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/16
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	109 mm
Dimension - Outside Diameter inch	0.80 in
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.38
Dimension - Strip Length inch	2-1/16
Dimension - Stud Size inch	5/16 in
Dimension - Stud Size fraction	5/16
Dimension - Bolt Size fraction	5/16
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	2 in
Dimension - Z inch	0.37 in
Dimension - B Length inch	2.00 in
Dimension - Length Side B inch	4.62 in
Dimension - Diameter Min Size inch	1.71 in

Dimension - N inch	0.34 in	UPC	781810324493
Dimension - Inside Diameter inch	0.64 in	Material	Copper
Dimension - Bolt Size inch	0.3125	Plating Type	Tin - Electro Plated
Dimension - Length Overall inch	4.28 in	Finish Type	Tin-Plated
		UPC 14 Digit GTIN	00781810324493
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	25
Die Index	16	Pallet Quantity	8700
Feature - Barrel Type	Long	Carton Quantity	25
Feature - Barrel Style	• Chamfered • Skived	Product Assets	
Plated	Y	Catalog [English]	
Color Code	Yellow	Installation Manual [English]	
		Installation Manual [French, English]	



A Hubbell brand