



YAZV292NTCFX, Compression Terminal, 4/0 Flex Class I,K,M, 250 Code, 2-Hole, 1/2" Stud, Long Barrel

By Burndy

Catalog # [YAZV292NTCFX](#)

Copper Compression Terminal

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	250 KCMIL
Conductor - Copper Flex K Size	4/0 AWG
Range	
Conductor - Copper Flex K Size	"4/0 AWG"
Conductor - Copper Flex M Size	4/0 AWG
Range	
Conductor - Copper Flex M Size	"4/0 AWG"
Conductor - Copper Str Size	"4/0 AWG"
Conductor - Copper Flex I Size	4/0 AWG
Range	
Conductor - Copper Flex G Size	"4/0 AWG"
Conductor - Copper DLO Size	4/0 AWG
Range	
Conductor - Copper Str	"4/0 AWG"
Compact Size	
Conductor - Copper DLO Size	4/0 AWG
Conductor Size	250 KCMIL
Conductor - Copper Flex H Size	"4/0 AWG"
Conductor - Copper Flex G Size	4/0 AWG
Range	



Conductor - Copper Str Navy	200
Size	
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	250 kcmil
Range	
Conductor - Copper Flex H Size	4/0 AWG
Range	
Conductor - Copper Flex I Size	"4/0 AWG"

Configuration

Physical Attribute - Number of	2
Holes	
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.18 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	142 mm
mm	
Dimension - Outside Diameter	0.80 in
inch	
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Strip Length inch	2-1/16
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue	Straight
Angle	
Dimension - B Length fraction	2 in
Dimension - Z inch	0.65 in
Dimension - B Length inch	2.00 in
Dimension - N inch	0.62 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall	5.59 in
inch	

General

Trade Name	HYLUG™
Die Index	16
Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Y
Color Code	Yellow
UPC	781810235188
Type	Long Barrel, Skive
Material	Copper
Plating Type	Tin - Electro-Plated

Finish Type	Tin-Plated
UPC 12 Digit	781810235188
UPC 14 Digit GTIN	00781810235188

Logistics

Minimum Pack Quantity	50
Pallet Quantity	6000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)



A Hubbell brand