



YAZV2C2NT14E2FX, Compression Terminal, 2 Flex G, H, I, K, M, DLO, 2 AWG, Cu, 2-Hole, 1/4" Stud, 3/4" Spacing, Long Barrel, Narrow Tongue

By Burndy

Catalog # [YAZV2C2NT14E2FX](#)

2 Flex G,H,I,K,M,DLO, 2 AWG, CU, 2 Hole, 1/4 Stud, 3/4 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex M Size	"2 AWG"
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Str Compact Size	"2 AWG"
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	"2 AWG"



Conductor - Copper Flex G Size Range	2 AWG
Conductor - Copper Str Navy Size	60
Conductor - CopperWeld Str Size	• 2 A AWG • 2 F AWG • 2 G AWG • 2 J AWG • 2 K AWG • 2 N AWG • 2 P AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	"2 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.50 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	80 mm
Dimension - Outside Diameter inch	0.46 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	1-7/16
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4

Dimension - Bolt Hole Size inch	0.27 in		
Dimension - Bolt Size fraction	1/4		
Physical Attribute - Tongue Angle	Straight		• Skived
Dimension - B Length fraction	1-3/8 in	Plated	Y
Dimension - Z inch	0.34 in	Color Code	Brown
Dimension - B Length inch	1.38 in	Sub Brand	TERMINALS, HYLUG
Dimension - Diameter Min Size inch	1.40 in	UPC	781810248973
Dimension - N inch	0.31 in	Type	YAZV-2NTFX, Long Barrel
Dimension - Bolt Size inch	0.25	Material	Copper
Dimension - Length Overall inch	3.14 in	Plating Type	Tin - Electro Plated
		Finish Type	Tin-Plated
		UPC 14 Digit GTIN	00781810248973
General			
Trade Name	HYLUG™	Logistics	
Die Index	10	Minimum Pack Quantity	1
Feature - Barrel Type	Long	Carton Quantity	25
Feature - Barrel Style	• Chamfered	Product Assets	
		Catalog [English]	
		Installation Manual [English]	
		Installation Manual [French, English]	



A Hubbell brand