



YAZV2C2NTCFX, Compression Terminal, 2 Flex G,H,I,K,M, DLO, 2 AWG, Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Long Barrel

By Burndy

Catalog # [YAZV2C2NTCFX](#)

2 Flex G,H,I,K,M,DLO, 2 AWG, CU, 2 Hole, 1/2 Stud, 1-3/4 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex M Size Range	2 AWG
Conductor - Copper Flex M Size	"2 AWG"
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Str Compact Size	"2 AWG"
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	"2 AWG"
Conductor - Copper Flex G Size Range	2 AWG



Conductor - Copper Str Navy Size	60
Conductor - CopperWeld Str Size Range	2 A AWG-2 P AWG
Conductor - CopperWeld Str Size	• 2 A AWG • 2 F AWG • 2 G AWG • 2 J AWG • 2 K AWG • 2 N AWG • 2 P AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	"2 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.83 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	121 mm
Dimension - Outside Diameter inch	0.46 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56
Dimension - Strip Length inch	1-7/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in

Dimension - Bolt Size fraction	1/2	Color Code	Brown
Physical Attribute - Tongue	Straight	UPC	781810228326
Angle		Type	Long Barrel, Skive
Dimension - B Length fraction	1-3/8 in	Material	Copper
Dimension - Z inch	0.65 in	Plating Type	Tin
Dimension - B Length inch	1.38 in	Finish Type	Tin-Plated
Dimension - Length Side B inch	4.76 in	UPC 12 Digit	781810228326
Dimension - N inch	0.62 in	UPC 14 Digit GTIN	00781810228326
Dimension - Bolt Size inch	0.5		
Dimension - Length Overall	4.76 in		
inch			
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	10	Pallet Quantity	11600
Feature - Barrel Type	Long	Carton Quantity	25
Feature - Barrel Style	- Chamfered - Skived	Product Assets	
Plated	Y	Catalog [English]	
		Installation Manual [English]	
		Installation Manual [French, English]	
 A Hubbell brand		© 2026 Hubbell Incorporated. All rights reserved BRDY-YAZV2C2NTCFX-SPEC-EN REV 5/2026	