



YAZV2C2TC14FX, Cu Compression, 2-Hole, 1/4" Stud, 5/8" Spacing, Long Barrel, 2 Flex G, H, I, K, M, DLO, 2 AWG

By Burndy

Catalog # [YAZV2C2TC14FX](#)

2 Flex G,H,I,K,M,DLO, 2 AWG, CU, 2 Hole, 1/4 Stud, 5/8 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex M Size Range	2 AWG
Conductor - Copper Flex M Size	"2 AWG"
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Str Compact Size	"2 AWG"
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	"2 AWG"



Conductor - Copper Flex G Size Range	2 AWG
Conductor - Copper Str Navy Size	60
Conductor - CopperWeld Str Size Range	2 A AWG-2 P AWG
Conductor - CopperWeld Str Size	• 2 A AWG • 2 F AWG • 2 G AWG • 2 J AWG • 2 K AWG • 2 N AWG • 2 P AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	"2 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.68 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	76 mm
Dimension - Outside Diameter inch	0.46 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	1-7/16
Dimension - Stud Size fraction	1/4

Dimension - Bolt Hole Size inch	0.27 in	Color Code	Brown
Dimension - Bolt Size fraction	1/4	Sub Brand	HYLUG
Physical Attribute - Tongue Angle	Straight	UPC	781810228289
Dimension - B Length fraction	1-3/8 in	Type	Long Barrel, Skive
Dimension - Z inch	0.34 in	Material	Copper
Dimension - B Length inch	1.38 in	Plating Type	Tin
Dimension - Length Side B inch	3.01 in	Finish Type	Tin-Plated
Dimension - N inch	0.31 in	UPC 12 Digit	781810228289
Dimension - Bolt Size inch	0.25	UPC 14 Digit GTIN	00781810228289
Dimension - Length Overall inch	3.01 in		
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	10	Carton Quantity	25
Feature - Barrel Type	Long	Product Assets	
Feature - Barrel Style	Skived	Catalog [English]	
Plated	Y	Installation Manual [English]	
		Installation Manual [French, English]	



A Hubbell brand