



YAZV2CTC12FX, Compression Terminal, 2 Flex G,H,I,K,M, DLO, 2 AWG, Cu, 1-Hole, 1/2" Stud, Long Barrel

By Burndy

Catalog # [YAZV2CTC12FX](#)

2 Flex G,H,I,K,M,DLO, 2 AWG, CU, 1 Hole, 1/2 Stud, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex M Size Range	2 AWG
Conductor - Copper Flex M Size	"2 AWG"
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Str Compact Size	"2 AWG"
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG



Conductor - Copper Flex H Size	"2 AWG"
Conductor - Copper Flex G Size Range	2 AWG
Conductor - Copper Str Navy Size	60
Conductor - CopperWeld Str Size Range	2 A AWG-2 P AWG
Conductor - CopperWeld Str Size	• 2 A AWG • 2 F AWG • 2 G AWG • 2 J AWG • 2 K AWG • 2 N AWG • 2 P AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	"2 AWG"

Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.77 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	73 mm
Dimension - Outside Diameter inch	0.46 in
Dimension - Hole Size mm	13.5 mm
Dimension - Hole Size inch	0.53
Dimension - Strip Length inch	1-7/16

Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-3/8 in
Dimension - Z inch	0.55 in
Dimension - B Length inch	1.38 in
Dimension - N inch	0.53 in
Dimension - Bolt Size inch	0.5
Dimension - Length Overall inch	2.87 in

General

Trade Name	HYLUG™
Die Index	10
Feature - Barrel Type	Long
Feature - Barrel Style	Skived



A Hubbell brand

Plated	Y
Color Code	Brown
Sub Brand	HYLUG
UPC	781810241318
Type	Long Barrel, Skive
Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810241318
UPC 14 Digit GTIN	00781810241318

Logistics

Minimum Pack Quantity	1
Carton Quantity	25

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)