



YAZV4C2TC14FX45, Compression Terminal, 4 Flex G,H,I,K,M, DLO, 4 AWG Cu, 2-Hole, 1/4" Stud, 5/8" Spacing, Long Barrel, 45 Degree

By Burndy

Catalog # [YAZV4C2TC14FX45](#)

4 Flex G,H,I,K,M,DLO, 4 AWG, CU, 2 Hole, 1/4 Stud, 5/8 IN Spacing, Long Barrel, Inspection Window, 45 Degree

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	4 AWG
Conductor - Copper Flex K Size Range	4 AWG
Conductor - Copper Flex K Size	"4 AWG"
Conductor - Copper Flex M Size Range	4 AWG
Conductor - Copper Flex M Size	"4 AWG"
Conductor - Copper Str Size	"4 AWG"
Conductor - Copper Flex I Size Range	4 AWG
Conductor - Copper Flex G Size	"4 AWG"
Conductor - Copper DLO Size Range	4 AWG
Conductor - Copper Str Compact Size	"4 AWG"
Conductor - Copper DLO Size	4 AWG
Conductor Size	4 AWG
Conductor - Copper Flex H Size	"4 AWG"



Conductor - Copper Flex G Size Range	4 AWG
Conductor - Copper Str Navy Size	40
Conductor - CopperWeld Str Size Range	4 A AWG-4 P AWG
Conductor - CopperWeld Str Size	• 4 A AWG • 4 D AWG • 4 N AWG • 4 P AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	4 AWG
Conductor - Copper Flex H Size Range	4 AWG
Conductor - Copper Flex I Size	"4 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.55 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4
Dimension - Height inch	1.37 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	66 mm
Dimension - Outside Diameter inch	0.38 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in

Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	45 Degree
Angle - Pad	45 °
Dimension - B Length fraction	1-1/4 in
Dimension - Z inch	0.33 in
Dimension - B Length inch	1.25 in
Dimension - N inch	0.31 in
Dimension - Bolt Size inch	0.25
Dimension - Length Overall inch	2.59 in

General

Trade Name	HYLUG™
Die Index	8
Feature - Barrel Type	Long
Feature - Barrel Style	Skived

Plated	Y
Color Code	Gray
UPC	781810230534
Type	Long Barrel, Skive
Material	Copper
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810230534
UPC 14 Digit GTIN	00781810230534

Logistics

Minimum Pack Quantity	50
Pallet Quantity	23200
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)



A Hubbell brand