



YAZV4C2TC38E2FX, Compression Terminal, 4 Flex, G,H,I,K,M, DLO, 4 AWG, Cu, 2-Hole, 3/8" Stud, 3/4" Spacing, Long Barrel

By Burndy

Catalog # [YAZV4C2TC38E2FX](#)

4 Flex G,H,I,K,M,DLO, 4 AWG, CU, 2 Hole, 3/8 Stud, 3/4 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	4 AWG
Conductor - Copper Flex K Size Range	4 AWG
Conductor - Copper Flex K Size	"4 AWG"
Conductor - Copper Flex M Size Range	4 AWG
Conductor - Copper Flex M Size	"4 AWG"
Conductor - Copper Str Size	"4 AWG"
Conductor - Copper Flex I Size Range	4 AWG
Conductor - Copper Flex G Size	"4 AWG"
Conductor - Copper DLO Size Range	4 AWG
Conductor - Copper Str Compact Size	"4 AWG"
Conductor - Copper DLO Size	4 AWG
Conductor Size	4 AWG
Conductor - Copper Flex H Size	"4 AWG"



Conductor - Copper Flex G Size Range	4 AWG
Conductor - Copper Str Navy Size	40
Conductor - CopperWeld Str Size Range	4 A AWG-4 P AWG
Conductor - CopperWeld Str Size	• 4 A AWG • 4 D AWG • 4 N AWG • 4 P AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	4 AWG
Conductor - Copper Flex H Size Range	4 AWG
Conductor - Copper Flex I Size	"4 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.58 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	80 mm
Dimension - Outside Diameter inch	0.38 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8

Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-1/4 in
Dimension - Z inch	0.43 in
Dimension - B Length inch	1.25 in
Dimension - Length Side B inch	3.14 in
Dimension - N inch	0.41 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	3.14 in

General

Trade Name	HYLUG™
Die Index	8
Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Y

Color Code	Gray
UPC	781810273937
Type	Long Barrel, Skive
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810273937
UPC 14 Digit GTIN	00781810273937

Logistics

Minimum Pack Quantity	50
Carton Quantity	50

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand