



YAZV6C2TC10FX, Compression Terminal, 6 61/24 DLO, 6 AWG Code, 2-Hole, #10 Stud, 5/8" Spacing, Long Barrel

By Burndy

Catalog # [YAZV6C2TC10FX](#)

2 Hole HYLUG Cu Compr Terminal, Long Brrl, W/ Insp Window, 6(61/#24) DLO, #6 AWG Code, #10 stud, 5/8" spacing, Blue

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	6 AWG
Conductor - Copper Flex K Size Range	6 AWG
Conductor - Copper Flex K Size	"6 AWG"
Conductor - Copper Flex M Size Range	6 AWG
Conductor - Copper Flex M Size	"6 AWG"
Conductor - Copper Str Size	"6 AWG"
Conductor - Copper Flex I Size Range	6 AWG
Conductor - Copper Flex G Size	"6 AWG"
Conductor - Copper DLO Size Range	6 AWG
Conductor - Copper Str Compact Size	"6 AWG"
Conductor - Copper DLO Size	6 AWG
Conductor Size	6 AWG
Conductor - Copper Flex H Size	"6 AWG"
Conductor - Copper Flex G Size	6 AWG
Range	



Conductor - Copper Str Navy Size	30
Conductor - CopperWeld Str Size Range	6 A AWG-6 D AWG
Conductor - CopperWeld Str Size	• 6 A AWG • 6 C AWG • 6 D AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	6 AWG
Conductor - Copper Flex H Size Range	6 AWG
Conductor - Copper Flex I Size	"6 AWG"

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.48 in
Package Height	0.000 in
Dimension - Hole Size fraction	#10
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	53 mm
Dimension - Outside Diameter inch	0.31 in
Dimension - Hole Size mm	5.3 mm
Dimension - Hole Size inch	0.21
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size fraction	#10
Dimension - Bolt Hole Size inch	0.20 in
Dimension - Bolt Size fraction	#8-#10
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	5/8
Dimension - Z inch	0.28 in

Dimension - B Length inch	0.625 in	Type	Long Barrel, Skive
Dimension - N inch	0.25 in	Material	Copper
Dimension - Bolt Size inch	0.21	Plating Type	Tin
Dimension - Length Overall inch	2.10 in	Finish Type	Tin-Plated
		UPC 12 Digit	781810228104
		UPC 14 Digit GTIN	00781810228104
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	100
Die Index	7	Carton Quantity	100
Feature - Barrel Type	Long		
Feature - Barrel Style	Skived		
Plated	Y	Product Assets	
Color Code	Blue	Catalog [English]	
UPC	781810228104		

