



YBM26L3BR, Uninsulated Flag-Type Ring Terminal For 2/0 AWG

By Burndy
Catalog # [YBM26L3BR](#)

Uninsulated Flag-Type Ring Terminal For 2/0 AWG

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally provides for a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Specifications

Standards - RoHS Compliance CM
Status

Conductor

Conductor - Copper Str Aircraft AN 2/0
Size
Conductor Size 2/0 AWG
Conductor - Copper Str Size 2/0
Conductor - Copper Str Size 2/0 AWG
Range
Conductor Type • CU C Solid-Size
 • CU C Str-Size

Configuration

Physical Attribute - Number of 1
Holes
Connector Type Flag Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	7/8 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.84 in
Dimension - Outside Diameter inch	0.76 in
Dimension - Z inch	0.61 in
Dimension - Pad Width inch	0.91 in
Physical Attribute - Tongue Angle	90 Degree
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Stud Size inch	1/2 in
Dimension - Length Overall inch	1.96 in
Dimension - N inch	0.48 in

General

Die Index	598
Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG™
Plated	N
Feature - Barrel Style	Chamfered
UPC 14 Digit GTIN	00781810460825
Material	Copper
Plating Type	Unplated
UPC	781810460825

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	19600

Product Assets

[Catalog \[English\]](#)