



YBM2CL1, Uninsulated Flag-Type Ring Terminal For 2 AWG

By Burndy
Catalog # [YBM2CL1](#)

Uninsulated Flag-Type Ring Terminal For 2 AWG



Features

- Made of pure electrolytic copper for maximum conductivity and ductility
- Seamless extrusion tin plated to resist corrosion
- Beveled barrel for easy wire entry

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size	AN 2
Conductor - Copper DLO Size	2 (150/#24)
Conductor Size	2 AWG
Conductor - Copper Str Size	2
Conductor - Copper Str Size Range	2 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Flex I Size	2

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Flag Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in

Dimension - B Length fraction	11/16 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.59 in
Dimension - Outside Diameter inch	0.53 in
Dimension - Z inch	0.36 in
Dimension - Pad Width inch	0.66 in
Physical Attribute - Tongue Angle	90 Degree
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Strip Length inch	5/8
Dimension - Stud Size inch	1/4
Dimension - Length Overall inch	1.28 in
Dimension - N inch	0.3 in

General

Die Index	57
Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
UPC 14 Digit GTIN	00781810026243
Material	Copper
Plating Type	Tin
UPC	781810026243

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	76800

Product Assets

[Catalog \[English\]](#)