



YBM4CL, Uninsulated Flag-Type Ring Terminal For 4 AWG

By Burndy
Catalog # [YBM4CL](#)

Uninsulated Flag-Type Ring Terminal For 4 AWG

Features

- Made of pure electrolytic copper for maximum conductivity and ductility
- Seamless extrusion tin plated to resist corrosion
- Beveled barrel for easy wire entry

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size	AN 4
Conductor - Copper DLO Size	4 (105/#24)
Conductor Size	4 AWG
Conductor - Copper Str Size	4
Conductor - Copper Str Size Range	4 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Flex I Size	4

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Flag Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in

Dimension - B Length fraction	9/16 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.47 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Z inch	0.36 in
Dimension - Pad Width inch	0.53 in
Physical Attribute - Tongue Angle	90 Degree
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	1/4
Dimension - Length Overall inch	1.21 in
Dimension - N inch	0.3 in

General

Die Index	56
Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
UPC 14 Digit GTIN	00781810026250
Material	Copper
Plating Type	Tin
UPC	781810026250

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	96000

Product Assets

[Catalog \[English\]](#)