



YBM4CL4, Uninsulated Flag-Type Ring Terminal For 4 AWG

By Burndy
Catalog # [YBM4CL4](#)

Uninsulated Flag-Type Ring Terminal For 4 AWG

Features

- Made of pure electrolytic copper for maximum conductivity and ductility
- Seamless extrusion tin plated to resist corrosion
- Beveled barrel for easy wire entry

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size	AN 4
Conductor - Copper DLO Size	4 (105/#24)
Conductor Size	4 AWG
Conductor - Copper Str Size	4
Conductor - Copper Str Size Range	4 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Flex I Size	4

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Flag Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	9/16 in

Package Weight	0.000 lb.
Dimension - B Length inch	0.47 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Z inch	0.36 in
Dimension - Pad Width inch	0.53 in
Physical Attribute - Tongue Angle	90 Degree
Package Height	0.000 in
Dimension - Bolt Hole Size inch	0.2 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	• #8 • #10
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.27 in

General

Die Index	56
Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
UPC 14 Digit GTIN	00781810026267
Material	Copper
Plating Type	Tin
UPC	781810026267

Logistics

Minimum Pack Quantity	100
Carton Quantity	800
Pallet Quantity	76800

Product Assets

[Catalog \[English\]](#)