



YC1L12TN, Compression C-Tap, Main #1-#3 AWG, Tap #3-#12 AWG, Tin Plated

By Burndy
Catalog # [YC1L12TN](#)

Cu Thin Wall C-Tap, Compression, #1 - #3 AWG(Main), #3 - #12 AWG(Tap), 600 V, Tin Plated

Features

- Material is high conductivity wrought copper providing low resistance for excellent electrical conductivity
- Reinforced ribs on the outside of the connector increase the mechanical strength of the connection
- Creates a compact connection that is easy for taping and insulating
- Connectors are clearly marked with color code dot, UL and CSA (when applicable), wire size, and die index number

Application

Wire Tap

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	1 AWG-12 AWG
Conductor - Copper Str Run Range	1 AWG-3 AWG
Conductor - Copper Str Run	1 AWG-3 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Tap Range	4 AWG-12 AWG
Conductor - Copper Str Tap	4 AWG-12 AWG

Configuration

Connector Type	C-TAP
----------------	-------



Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.34 in
Package Height	0.000 in
Dimension - B Length fraction	9/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.55 in
Dimension - D inch	1.75 in
Dimension - Strip Length inch	1-13/16

General

Plated	Y
Color Code	Black
Trade Name	CRIMPIT™
Die Index	13
UPC	781810040232
Type	YC-L Series
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810040232
UPC 14 Digit GTIN	00781810040232

Logistics

Minimum Pack Quantity	150
Pallet Quantity	27750
Carton Quantity	150

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)