

YC1U1, Figure 6-Shape Connector

By Burndy
Catalog # [YC1U1](#)



Figure 6- shaped, wide range-taking aluminum compression tap connector

Features

- Figure 6-shaped
- Wide range-taking aluminum compression tap connector
- Run: Al & Cu: 2 - 1 kcmil, ACSR: 2
- Tap: 6 - 1 AWG, ACSR: 6 -2

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	2 AWG-1 AWG
Conductor - Copper Solid Tap Range	6 AWG
Conductor - AL Str Run Range	2 AWG - 1 AWG
Conductor - AL Str Tap Range	6 AWG-2 AWG
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor - ACSR Str Run	2 Str
Conductor - ACSR Str Tap	6 AWG - 2 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	1.62 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in

General

Plated	N
Trade Name	CRIMPIT™
Die Index	D
UPC	781810121252
Type	YC-A, YC-U Series
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810121252
UPC 14 Digit GTIN	00781810121252

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)