



YC25A2, Aluminum C-Shape Connector

By Burndy
Catalog # [YC25A2](#)

Range-taking, C-shaped AL compression tap



Features

- Range-taking, C-shaped AL compression tap
- Run: Aluminum: 1/0, ACSR: 2
- Tap: Aluminum: 1/0, ACSR: 2

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run	1/0 AWG
Conductor - AL Str Tap Range	2 Sol. - 2 Str.
Conductor - AL Str Tap	2 AWG
Conductor - ACSR Str Run	1/0 Str
Conductor - ACSR Str Tap	2 (6-1) - 2 (7-1)
Range	
Conductor - ACSR Str Tap	2 (6-1) - 2 (7-1)

Dimensions

Dimension - Height mm	0 mm
Length	2.25 in

Dimension - Height inch	1.00 in
Dimension - L Length Overall mm	57 mm
Height	2.25 in
Width	1 in
Dimension - Length Overall inch	2.25 in
Dimensions	2.25 in x 1 in x 2.25 in

General

Plated	N
Trade Name	CRIMPIT™
Die Index	C
UPC	781810123300
Type	YC-A, YC-U Series
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810123300
UPC 14 Digit GTIN	00781810123300

Logistics

Minimum Pack Quantity	1
Pallet Quantity	14800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)