



YC25A25, Aluminum C-Shape Connector

By Burndy
Catalog # [YC25A25](#)

Range-taking, C-shaped AL compression tap



Features

- Range-taking, C-shaped AL compression tap
- Run: Aluminum: 1/0- 2/0, ACSR: 1/0
- Tap: Aluminum: 1/0- 2/0, ACSR: 1/0

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	1/0 AWG - 2/0 AWG
Conductor - AL Str Run	• 1/0 AWG • 2/0 AWG
Conductor - AL Str Tap Range	1/0 AWG - 2/0 AWG
Conductor - AL Str Tap	• 1/0 AWG • 2/0 AWG
Conductor - ACSR Str Run	1/0 Str
Conductor - ACSR Str Tap	1/0 Str

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Length	1.75 in
Dimension - Height inch	1.36 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	44 mm
Height	1.75 in
Width	1.36 in
Dimension - Length Overall inch	1.75 in
Dimensions	1.75 in x 1.36 in x 1.75 in

General

Plated	N
Trade Name	CRIMPIT™
Die Index	Q
UPC	781810123621
Type	YC-A, YC-U Series
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810123621
UPC 14 Digit GTIN	00781810123621

Logistics

Minimum Pack Quantity	50
Pallet Quantity	14800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)