



YC25A4, Aluminum C-Shape Connector

By Burndy
Catalog # [YC25A4](#)

Range-taking, C-shaped AL compression tap



Features

- Al Compression Tap (C-Shaped)
- 1/0 Str. Al/ACSR (Run)
- #6 - #4 Str. Al/ACSR (Tap)

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run	1/0 AWG
Conductor - AL Str Tap Range	6 AWG - 4 AWG
Conductor - AL Str Tap	• 6 AWG • 4 AWG
Conductor - ACSR Str Run	1/0 Str
Conductor - ACSR Str Tap Range	6 AWG - 4 AWG

Dimensions

Dimension - Height mm	0 mm
Length	1.5 in

Dimension - Height inch	1.00 in
Dimension - L Length Overall mm	38 mm
Height	1.5 in
Width	1 in
Dimension - Length Overall inch	1.50 in
Dimensions	1.5 in x 1 in x 1.5 in

General

Plated	N
Trade Name	CRIMPIT™
Die Index	C
UPC	781810123607
Type	YC-A, YC-U Series
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810123607
UPC 14 Digit GTIN	00781810123607

Logistics

Minimum Pack Quantity	1
Pallet Quantity	23200
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)