

YC25L12, Cu Compression C-Tap, Thin Wall

By Burndy

Catalog # [YC25L12](#)

Copper Compression C Tap, Thin Wall, 1 AWG (Run), 4-3 AWG (Tap)



Features

- Material is high conductivity wrought copper providing low resistance for excellent electrical conductivity
- Bare copper range taking connector allows for less inventory
- Reinforced ribs on the outside of the connector increase the mechanical strength of the connection
- Creates a compact connection that is easy for taping and insulating
- Connectors are clearly marked with color code dot, UL and CSA (when applicable), wire size, and die index number

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor Size	1/0 AWG-12 AWG
Conductor - Copper Str Run Range	1/0 AWG-2 AWG
Conductor - Copper Str Run	1/0 AWG-2 AWG
Conductor - Copper Solid Run Range	2 AWG-1/0 AWG
Conductor - Copper Solid Run	• 2 AWG • 1 AWG • 1/0 AWG
Conductor - Copper Solid Tap Range	12 AWG-2 AWG
Conductor - Copper Solid Tap	• 12 AWG • 11 AWG • 10 AWG • 9 AWG

- 8 AWG
- 7 AWG
- 6 AWG
- 5 AWG
- 4 AWG
- 3 AWG
- 2 AWG

Conductor Type	CODE
Conductor - Copper Str Tap Range	3 AWG-12 AWG
Conductor - Copper Str Tap	3 AWG-12 AWG

Configuration

Connector Type	C-TAP
----------------	-------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.42 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Strip Length inch	1-13/16
Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.62 in
Dimension - D inch	1.75 in

General

Trade Name	CRIMPIT™
Die Index	14
Plated	Y
Color Code	Orange
Sub Brand	CRIMPIT
UPC	781810040171
Type	YC-L Series
Material	Copper
Plating Type	Tin - Bright
Finish Type	Tin-Plated
UPC 12 Digit	781810040171
UPC 14 Digit GTIN	00781810040171

Logistics

Minimum Pack Quantity	1
-----------------------	---

Pallet Quantity	23200	Temperature Rating	194
Carton Quantity	50		

Operational

Product Assets

[Catalog \[English\]](#)



A Hubbell brand