

YC26A2, Aluminum C-Shape Connector

By Burndy

Catalog # YC26A2



Range-taking, C-shaped AL compression tap

Features

- Al Compression Tap (C-Shaped)
- 1/0 - 2/0 Str.Al/ACSR (Run)
- #2 Str.Al/ACSR (Tap)

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	1/0 AWG - 2/0 AWG
Conductor - AL Str Tap	2 Str
Conductor - ACSR Str Run	2 AWG
Conductor - ACSR Str Tap	2 Str

Dimensions

Dimension - Height mm	0 mm
Length	2.56 in
Dimension - Height inch	1.38 in

Dimension - L Length Overall	65 mm
mm	
Height	2.56 in
Width	1.38 in
Dimension - Length Overall	2.56 in
inch	
Dimensions	2.56 in x 1.38 in x 2.56 in

General

Plated	N
Trade Name	CRIMPIT™
UPC	781810105054
Type	YC-A, YC-U Series
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810105054
UPC 14 Digit GTIN	00781810105054

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7200
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)