

YC26A25, Aluminum C-Shape Connector

By Burndy
Catalog # [YC26A25](#)

Range-taking, C-shaped AL compression tap



Features

- Range-taking, C-shaped AL compression tap
- Run: Aluminum: 1/0- 2/0, ACSR: 1/0-2/0
- Tap: Aluminum: 1/0- 1/0, ACSR: 1/0-1/0

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	1/0 AWG - 2/0 AWG
Conductor - AL Str Run	• 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - AL Str Tap Range	1/0 AWG - 1/0 AWG
Conductor - AL Str Tap	1/0 AWG
Conductor - ACSR Str Run Range	1/0 AWG - 2/0 AWG
Conductor - ACSR Str Tap	1/0 AWG - 1/0 AWG

Dimensions

Dimension - Height mm	0 mm
-----------------------	------

Length	2.56 in
Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	65 mm
Height	2.56 in
Width	1.38 in
Dimension - Length Overall inch	2.56 in
Dimensions	2.56 in x 1.38 in x 2.56 in

General

Plated	N
Trade Name	CRIMPIT™
Die Index	D
UPC	781810124529
Type	YC-A, YC-U Series
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810124529
UPC 14 Digit GTIN	00781810124529

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7200
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)