



YC26A26, Aluminum C-Shape Connector

By Burndy
Catalog # [YC26A26](#)

Range-taking, C-shaped AL compression tap



Features

- Range-taking C-shaped aluminum compression tap, or dead-ending connector, designed to eliminate effects of cold flow
- Connector can be gripped in tool and slipped over line for easy crimping
- Pre-filled with PENETROX joint compound and strip sealed

Application

For Combinations Of Aluminum, ACSR, 6201, 5005, Compressed and Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	1/0 AWG - 2/0 AWG
Conductor - AL Str Run	• 1/0 AWG • 2/0 AWG
Conductor - AL Str Tap Range	2/0 AWG
Conductor - AL Str Tap	2/0 Str
Conductor - ACSR Str Run Range	1/0 AWG - 2/0 AWG
Conductor - ACSR Str Tap	2/0 Str

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	1.38 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	65 mm
Width	1.38 in
Length	2.56 in
Height	2.56 in
Dimension - Length Overall inch	2.56 in
Dimensions	2.56 in x 1.38 in x 2.56 in

General

Trade Name	CRIMPIT™
Die Index	D
Plated	N
Sub Brand	CRIMPIT
UPC	781810124826
Type	YC-A, YC-U Series
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810124826
UPC 14 Digit GTIN	00781810124826

Logistics

Minimum Pack Quantity	50
Pallet Quantity	7200
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)