



YC26A3, Aluminum C-Shape Connector

By Burndy
Catalog # [YC26A3](#)

Range-taking, C-shaped AL compression tap



Features

- Range-taking, C-shaped AL compression tap
- Run: Aluminum: 3/0- 4/0, ACSR: 3/0-4/0
- Tap: Aluminum: 6- 2, ACSR: 6-2

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	1/0 AWG - 2/0 AWG
Conductor - AL Str Tap Range	6 Str. - 2 Sol.
Conductor - ACSR Str Run Range	1/0 AWG - 2/0 AWG
Conductor - ACSR Str Tap Range	6 AWG - 4 AWG

Dimensions

Dimension - Height mm	0 mm
Length	2.56 in

Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	65 mm
Height	2.56 in
Width	1.38 in
Dimension - Length Overall inch	2.56 in
Dimensions	2.56 in x 1.38 in x 2.56 in

General

Plated	N
Trade Name	CRIMPIT™
Die Index	D
UPC	781810124222
Type	YC-A, YC-U Series
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810124222
UPC 14 Digit GTIN	00781810124222

Logistics

Minimum Pack Quantity	1200
-----------------------	------

Product Assets

[Catalog \[English\]](#)