



YC28A26, Aluminum C-Shape Connector

By Burndy
Catalog # [YC28A26](#)

Range-taking, C-shaped AL compression tap



Features

- Range-taking, C-shaped AL compression tap
- Run: Aluminum: 3/0- 4/0, ACSR: 3/0-4/0
- Tap: Aluminum: 2/0- 2/0, ACSR: 2/0-2/0

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	3/0 AWG-4/0 AWG
Conductor - ACSR Cmpt Run	• 3/0 AWG • 4/0 AWG
Conductor - AAAC 5005 Tap Range	155.4 (7) kcmil
Conductor - AAAC 5005 Tap	155.4 (7) kcmil
Conductor - AAAC 6201 Run Range	195.7 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 6201 Run	• 195.7 (7) kcmil • 246.9 (7) kcmil
Conductor - AAAC 6201 Tap Range	155.4 (7) kcmil
Conductor - AAAC 6201 Tap	155.4 (7) kcmil
Conductor - AL Str Run Range	3/0 AWG - 4/0 AWG
Conductor - AL Str Run	• 3/0 AWG • 4/0 AWG
Conductor - AAAC 5005 Run Range	195.7 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 5005 Run	• 195.7 (7) kcmil • 246.9 (7) kcmil
Conductor - AL Str Tap Range	2/0 AWG
Conductor - AL Str Tap	2/0 Str

Conductor - ACSR Cmpt Tap Range	2/0 AWG
Conductor - ACSR Cmpt Tap	2/0 AWG
Conductor - ACSR Str Run Range	3/0 AWG - 4/0 AWG
Conductor - ACSR Str Tap	2 Str

Dimensions

Dimension - Height mm	0 mm
Length	2.75 in
Dimension - Height inch	1.61 in
Dimension - L Length Overall mm	70 mm
Height	2.75 in
Width	1.61 in
Dimension - Length Overall inch	2.75 in
Dimensions	2.75 in x 1.61 in x 2.75 in

General

Plated	N
Trade Name	CRIMPIT™
Die Index	H
UPC	781810125724
Type	YC-A, YC-U Series
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810125724
UPC 14 Digit GTIN	00781810125724

Logistics

Minimum Pack Quantity	1
Pallet Quantity	6000
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)