



YC28U26, Figure 6-Shape Tap Connector

By Burndy
Catalog # YC28U26



Figure 6- shaped, wide range-taking aluminum compression tap connector

Features

- Figure 6- shaped, wide range-taking aluminum compression tap connector
- Run: Al & Cu: 1/0 - 4/0 kcmil, ACSR: 1/0 - 4/0
- Tap: 6 - 2/0 AWG, ACSR: 6 -1/0

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	1/0 -4/0 AWG
Conductor - Copper Solid Run Range	18 AWG
Conductor - Copper Solid Run Range	18 AWG
Conductor - Copper Solid Tap Range	6 AWG
Conductor - AL Str Run Range	1/0 AWG - 4/0 AWG
Conductor - AL Str Tap Range	6 AWG - 2/0 AWG
Conductor - Copper Str Tap Range	6 AWG - 2/0 AWG
Conductor - ACSR Str Run Range	1/0 AWG - 4/0 AWG
Conductor - ACSR Str Tap Range	6 AWG - 1/0 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	2.06 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.12 in

General

Plated	N
Trade Name	CRIMPIT™
Die Index	H
UPC	781810126479
Type	YC-A, YC-U Series
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810126479
UPC 14 Digit GTIN	00781810126479

Logistics

Minimum Pack Quantity	1
Pallet Quantity	6000
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)