

YC2A4, Aluminum C-Shape Connector

By Burndy
Catalog # [YC2A4](#)

Range-taking, C-shaped AL compression tap, or dead-ending connector designed to eliminate the effects of cold flow, "C" Die index



Features

- Range-taking C-shaped aluminum compression tap, or dead-ending connector, designed to eliminate effects of cold flow
- Connector can be gripped in tool and slipped over line for easy crimping
- Pre-filled with PENETROX joint compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	4 AWG-2 AWG
Conductor - ACSR Cmpt Run	• 4 AWG • 3 AWG • 2 AWG
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil
Conductor - AAAC 5005 Tap	30.58 (7) kcmil
Conductor - AAAC 6201 Run Range	48.69 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 6201 Run	• 48.69 (7) kcmil • 77.47 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil
Conductor - AL Str Run Range	2 Sol. - 2 Str
Conductor - AL Str Run	2 AWG
Conductor - AAAC 5005 Run Range	48.69 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 5005 Run	• 48.69 (7) kcmil • 77.47 (7) kcmil
Conductor - AL Str Tap Range	4 Sol. - 4 Str.

Conductor - AL Str Tap	4 AWG
Conductor - ACSR Cmpt Tap Range	6 AWG
Conductor - ACSR Cmpt Tap	6 AWG
Conductor - ACSR Str Run Range	4 AWG - 2 AWG
Conductor - ACSR Str Tap	6 Str

Dimensions

Dimension - Height mm	0 mm
Length	1.5 in
Dimension - Height inch	1.00 in
Dimension - L Length Overall mm	38 mm
Height	1.5 in
Width	1 in
Dimension - Length Overall inch	1.50 in
Dimensions	1.5 in x 1 in x 1.5 in

General

Plated	N
Trade Name	CRIMPIT™
Die Index	C
UPC	781810122105
Type	YC-A, YC-U Series
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810122105
UPC 14 Digit GTIN	00781810122105

Logistics

Minimum Pack Quantity	1
Pallet Quantity	29600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)