


YC2C2, Copper C-Shape Connector

By Burndy
Catalog # [YC2C2](#)

CU Compression C Shape Compression Connector



Features

- Range-taking connector lowering inventory requirements
- Compact size, easy to tape and insulate connection
- High conductivity wrought copper provides low resistance and excellent electrical conductivity

Application

For Range Of Copper And Making Tap Or Parallel Copper Connections

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	• UL 486A • UL486B
Certification - ETL	No
Standards - Industry Standards Met	• UL 486A • UL486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	2 Sol. - 2 Str
Conductor - Copper Str Run	2 AWG
Conductor - Copper Solid Run	2 AWG
Range	
Conductor - Copper Solid Run	2 AWG
Conductor - Copper Solid Tap	2 AWG
Range	
Conductor - Copper Solid Tap	2 AWG
Conductor Type	Cu C Sol-Size
Conductor - Copper Str Tap Range	2 Sol. - 2 Str

Conductor - Copper Str Tap 2 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	1.05 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	17 mm
Dimension - Length Overall inch	0.67 in

General

Product Family	Power Connectors>Copper Compression Terminals & Splices>C Taps>Heavy Wall CRIMPIT™
Trade Name	C
Die Index	No
Plated	CRIMPIT
Sub Brand	Compression
Product Type	781810111505
UPC	YC-C Series
Type	Copper
Material	Unplated
Plating Type	781810111505
UPC 12 Digit	00781810111505
UPC 14 Digit GTIN	

Logistics

Minimum Pack Quantity	1
Pallet Quantity	23200
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)