



YC2L12TN, Compression C-Tap, Main #2-#4 AWG, Tap #4-#12 AWG, Tin Plated

By Burndy
Catalog # [YC2L12TN](#)



Cu Thin Wall C-Tap, Compression, #2 - #4 AWG(Main), #4 - #12 AWG(Tap), 600 V, Tin Plated

Features

- Material is high conductivity wrought copper providing low resistance for excellent electrical conductivity
- Reinforced ribs on the outside of the connector increase the mechanical strength of the connection
- Creates a compact connection that is easy for taping and insulating
- Connectors are clearly marked with color code dot, UL and CSA (when applicable), wire size, and die index number

Application

Wire Tap

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	2 AWG-12 AWG
Conductor - Copper Str Run Range	2 AWG-4 AWG
Conductor - Copper Str Run	2 AWG-4 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Tap Range	4 AWG-12 AWG
Conductor - Copper Str Tap	4 AWG-12 AWG

Configuration

Connector Type	C-TAP
----------------	-------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.36 in
Package Height	0.000 in
Dimension - B Length fraction	1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.50 in
Dimension - D inch	1.18 in
Dimension - Strip Length inch	1-3/16

General

Plated	Y
Color Code	Yellow
Trade Name	CRIMPIT™
Die Index	12
UPC	781810040225
Type	YC-L Series
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810040225
UPC 14 Digit GTIN	00781810040225

Logistics

Minimum Pack Quantity	400
Pallet Quantity	48000
Carton Quantity	400

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)