



# BURNDY

## YC33R26, Aluminum C-Shape Connector

By Burndy

Catalog # [YC33R26](#)

Range-taking, C-shaped AL compression tap, or dead-ending connector



## Features

- Al Compression Tap (C-Shaped)
- 300-397.5 kcmil Al, 336.4 kcmil ACSR (Run)
- 2 -2/0 Str. Al, 2 -1/0 AWG ACSR (Tap)

## Specifications

Certification - ETL

No

Certification - UL Recognized

No

Standards - RoHS Compliance Status

CM  
Certification - cULus  
No  
UL Listed  
No  
Certification - CSA Approved  
No

Conductor

Conductor - ACSR Cmpt Run Range  
336.4 kcmil  
Conductor - ACSR Cmpt Run  
336.4 kcmil  
Conductor - AAAC 5005 Tap Range  
77.47 (7) kcmil-123.3 (7) kcmil  
Conductor - AAAC 5005 Tap

- 77.47 (7) kcmil
- 123.3 (7) kcmil

Conductor - AAAC 6201 Run Range  
394.5 (19) kcmil  
Conductor - AAAC 6201 Run  
394.5 (19) kcmil  
Conductor - AAAC 6201 Tap Range  
77.47 (7) kcmil-123.3 (7) kcmil  
Conductor - AAAC 6201 Tap

- 77.47 (7) kcmil
- 123.3 (7) kcmil

Conductor - AL Str Run Range  
300 kcmil-397 kcmil  
Conductor - AL Str Run  
336.4 Kcmil  
Conductor - AAAC 5005 Run Range  
394.5 (19) kcmil  
Conductor - AAAC 5005 Run  
394.5 (19) kcmil  
Conductor - AL Str Tap Range  
2 AWG - 2/0 AWG  
Conductor - AL Str Tap

- 2 AWG
- 1 AWG
- 1/0 AWG
- 2/0 AWG

Conductor - ACSR Cmpt Tap Range  
2 AWG-1/0 AWG  
Conductor - ACSR Cmpt Tap

- 2 AWG
- 1 AWG
- 1/0 AWG

Conductor - ACSR Str Run  
336.4 Kcmil  
Conductor - ACSR Str Tap Range  
2 AWG - 1/0 AWG

Dimensions

Dimension - Height mm  
0 mm  
Length  
1.98 in  
Dimension - Height inch  
1.98 in  
Dimension - L Length Overall mm  
40 mm  
Height  
1.98 in  
Width  
1.5 in  
Dimension - Length Overall inch  
1.56 in  
Dimensions  
1.98 in x 1.5 in x 1.98 in

## General

Plated  
N  
Trade Name  
CRIMPIT™  
Die Index  
R  
UPC  
781810127001  
Type  
YC-A, YC-U Series  
Material  
Aluminum  
Plating Type  
Unplated  
UPC 12 Digit  
781810127001  
UPC 14 Digit GTIN  
00781810127001

## Logistics

Minimum Pack Quantity  
1  
Pallet Quantity  
6000  
Carton Quantity  
25

## Product Assets

[Catalog \[English\]](#)



