

## YC33R26U, Aluminum Figure 6-Shape Connector

By Burndy  
Catalog # [YC33R26U](#)



Figure 6- shaped, wide range-taking aluminum compression tap connector

### Features

- Figure 6- shaped, wide range-taking aluminum compression tap connector
- Run: Al & Cu: 300 -397.5 kcmil, ACSR: 266.8 -336.4 kcmil
- Tap: 6-2/0 AWG, ACSR: 4 -1/0

### Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

### Conductor

|                                    |                         |
|------------------------------------|-------------------------|
| Conductor - Copper Str Run Range   | 300 Kcmil - 397.5 Kcmil |
| Conductor - Copper Solid Run Range | 18 AWG                  |
| Conductor - Copper Solid Run Range | 18 AWG                  |
| Conductor - Copper Solid Tap Range | 6 AWG                   |
| Conductor - AL Str Run Range       | 300 Kcmil - 397.5 Kcmil |
| Conductor - AL Str Tap Range       | 6 AWG - 2/0 AWG         |
| Conductor - Copper Str Tap Range   | 6 AWG - 2/0 AWG         |
| Conductor - ACSR Str Run Range     | 6 AWG - 2/0 AWG         |
| Conductor - ACSR Str Tap Range     | 6 AWG - 1/0 AWG         |

### Dimensions

|                                 |           |
|---------------------------------|-----------|
| Package Height                  | 0.000 in  |
| Dimension - Height mm           | 0 mm      |
| Dimension - Height inch         | 2.25 in   |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 54 mm     |
| Dimension - Length Overall inch | 2.12 in   |

### General

|                   |                   |
|-------------------|-------------------|
| Plated            | N                 |
| Trade Name        | CRIMPIT™          |
| Die Index         | R                 |
| UPC               | 781810127100      |
| Type              | YC-A, YC-U Series |
| Material          | Aluminum          |
| Plating Type      | Unplated          |
| UPC 12 Digit      | 781810127100      |
| UPC 14 Digit GTIN | 00781810127100    |

### Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 6000 |
| Carton Quantity       | 25   |

### Product Assets

[Catalog \[English\]](#)