

YC3L12TN, Compression C-Tap, Main #3-#5 AWG, Tap #5-#12 AWG, Tin Plated

By Burndy
Catalog # [YC3L12TN](#)

Cu Thin Wall C-Tap, Compression, #3 - #5 AWG(Main), #5 - #12 AWG(Tap), 600 V, Tin Plated



Features

- Material is high conductivity wrought copper providing low resistance for excellent electrical conductivity
- Reinforced ribs on the outside of the connector increase the mechanical strength of the connection
- Creates a compact connection that is easy for taping and insulating
- Connectors are clearly marked with color code dot, UL and CSA (when applicable), wire size, and die index number

Application

Wire Tap

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	3 AWG-12 AWG
Conductor - Copper Str Run Range	3 AWG-5 AWG
Conductor - Copper Str Run	3 AWG-5 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Tap Range	5 AWG-12 AWG
Conductor - Copper Str Tap	5 AWG-12 AWG

Configuration

Connector Type	C-TAP
----------------	-------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.27 in
Package Height	0.000 in
Dimension - B Length fraction	7/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.46 in
Dimension - D inch	1.18 in
Dimension - Strip Length inch	1-3/16

General

Plated	Y
Color Code	Green
Trade Name	CRIMPIT™
Die Index	11
UPC	781810040218
Type	YC-L Series
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810040218
UPC 14 Digit GTIN	00781810040218

Logistics

Minimum Pack Quantity	200
Pallet Quantity	46400
Carton Quantity	200

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)