



YC4A4, Aluminum C-Shape Connector

By Burndy
Catalog # [YC4A4](#)



Range-taking, C-shaped AL compression tap, or dead-ending connector designed to eliminate the effects of cold flow, 1-1/4" L

Features

- Al Compression Tap (C-Shaped)
- 6 Sol. - 4 Str. Al, #6 ACSR (Run)
- 4 Sol. - 4 Str. Al, #6 ACSR (Tap)

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil
Conductor - AAAC 5005 Tap	30.58 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil
Conductor - AL Str Run Range	6 Sol. - 4 Str
Conductor - AL Str Run	• 6 AWG • 4 AWG
Conductor - AL Str Tap Range	4 Sol. - 4 Str.
Conductor - ACSR Str Run	6
Conductor - ACSR Str Tap	6

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Length	1.25 in

Dimension - Height inch	075 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	32 mm
Height	1.25 in
Width	0.75 in
Dimension - Length Overall inch	1.25 in
Dimensions	1.25 in x 0.75 in x 1.25 in

General

Plated	N
Trade Name	CRIMPIT™
Die Index	BG
UPC	781810122709
Type	YC-A, YC-U Series
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810122709
UPC 14 Digit GTIN	00781810122709

Logistics

Minimum Pack Quantity	1
Pallet Quantity	29600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)