



YC4C8, Copper C-Shape Connector

By Burndy
Catalog # [YC4C8](#)

CU Compression C Shape Compression Connector, 600 Volts to 35 kV,
Run: 6 Sol. - 4 Str., Tap: 8 Sol. - 8 Str.

Features

- Range-taking connector lowering inventory requirements
- Compact size, easy to tape and insulate connection
- High conductivity wrought copper provides low resistance and excellent electrical conductivity

Application

For Making Tap Or Parallel Copper Connections

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	• UL 486A • UL486B
Certification - ETL	No
Standards - Industry Standards Met	• UL 486A • UL486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	6 Sol. - 4 Str.
Conductor - Copper Solid Run Range	6 Sol. - 4 Str.
Conductor - Copper Solid Tap	8 AWG
Conductor Type	Cu C Sol-Size
Conductor - Copper Str Tap	8 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	0.73 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	16 mm
Dimension - Length Overall inch	0.62 in

General

Product Family	Power Connectors>Copper Compression Terminals & Splices>C Taps>Heavy Wall
Trade Name	CRIMPIT™
Die Index	BG or 5/8
Plated	No
Sub Brand	CRIMPIT
Product Type	Compression
UPC	781810114254
Type	YC-C Series
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810114254
UPC 14 Digit GTIN	00781810114254

Logistics

Minimum Pack Quantity	1
Pallet Quantity	57600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)