

YC4U1, Aluminum Figure 6-Shape Connector

By Burndy
Catalog # [YC4U1](#)



Figure 6- shaped, wide range-taking aluminum compression tap connector

Features

- Figure 6-shaped
- Wide range-taking aluminum compression tap connector
- Pre-filled with PENETROX Oxide Inhibitor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	4 AWG
Conductor - ACSR Cmpt Run	4 AWG
Conductor - Copper Str Run Range	4 Sol. - 4 Str.
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 5005 Tap	• 30.58 (7) kcmil • 48.69 (7) kcmil • 77.47 (7) kcmil
Conductor - AAAC 6201 Run Range	48.69 (7) kcmil
Conductor - AAAC 6201 Run	48.69 (7) kcmil
Conductor - Copper Solid Run Range	4 Sol. - 4 Str.
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 6201 Tap	• 30.58 (7) kcmil • 48.69 (7) kcmil • 77.47 (7) kcmil
Conductor - Copper Solid Tap Range	6 Sol. - 1 Str.
Conductor - AL Str Run Range	4 Sol. - 4 Str.
Conductor - AAAC 5005 Run Range	48.69 (7) kcmil

Conductor - AAAC 5005 Run	48.69 (7) kcmil
Conductor - AL Str Tap Range	6 Sol. - 1 Str.
Conductor - AL Str Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - ACSR Cmpt Tap Range	6 AWG-1 AWG
Conductor - ACSR Cmpt Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor - Copper Str Tap Range	6 Sol. - 1 Str.

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
Die Index	D
UPC	781810123102
Type	YC-A, YC-U Series
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810123102
UPC 14 Digit GTIN	00781810123102

Logistics

Minimum Pack Quantity	2000
Pallet Quantity	11600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)