



YCA252NDT, Copper compression terminal,
1/0 Stranded, 2-hole, 1/2" Stud, 1-3/4"
Spacing, Dip Tin Plate

By Burndy
Catalog # [YCA252NDT](#)

Cu Wire lug, 1/0 str, .56"stud, 5.34"L

Features

- Copper Compression Terminal
- 1/0 Stranded 2-hole, 1/2" Stud, 1-3/4" Spacing
- Dip Tin Plate

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	1/0
Range	
Conductor - Copper Str Size	1/0

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.91 in
Dimension - Hole Size fraction	5/9
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-4/7 in



Dimension - Z inch	0.62 in
Dimension - L Length Overall mm	136 mm
Dimension - B Length inch	1.57 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.34 in
Dimension - Strip Length inch	1 5/8

General

Plated	Y
Trade Name	HYLUG™
Die Index	165
UPC	781810081082
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810081082
UPC 14 Digit GTIN	00781810081082

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7400
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)