



YCA252NTN, Copper compression terminal, 2-holes, No Skive, 1/2" Stud, 1-3/4" Spacing, Tin Plated

By Burndy
Catalog # [YCA252NTN](#)

Cu Compression terminal, 2 holes W/O/insp Window, 1/0 AWG, 1/2"stud, 5.34"L

Features

- Copper Compression Terminal
- 2-hole pad
- No inspection window
- 1/0 AWG Cu
- 1/2" Studs

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	1/0
-----------------------------	-----

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.91 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/9
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-4/7 in



Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	2.37 in
Dimension - L Length Overall mm	136 mm
Dimension - B Length inch	1.57 in
Dimension - Outside Diameter inch	0.62 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.34 in
Dimension - Strip Length inch	1-5/8 in

General

Plated	Y
Trade Name	HYLUG™
Die Index	165
UPC	781810055861
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810055861

Logistics

Minimum Pack Quantity	50
Pallet Quantity	7400
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)