



YCA25R2N15, Aluminum Compression Lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing, 15 Degree Pad Angle

By Burndy
Catalog # [YCA25R2N15](#)

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 6.75 IN L

Features

- Aluminum Compression Lug
- 2-Hole, 1/2" Stud, 1-3/4" Spacing
- 15 Degree Pad Angle

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Dimension - B Length inch	2.39 in
Dimension - Outside Diameter inch	0.62 in



Dimension - L Length Overall mm	171 mm
Dimension - Pad Width inch	0.87 in
Dimension - Length Overall inch	6.75 in

General

Trade Name	HYLUG™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810660614
UPC 14 Digit GTIN	00781810660614
Material	Aluminum
Plating Type	Unplated
UPC	781810660614

Logistics

Minimum Pack Quantity	1
Carton Quantity	20
Pallet Quantity	5920

Product Assets

[Catalog \[English\]](#)