



# YCA262NW, Copper compression lug, 2/0 Str, 2-Hole, 1-3/4" Spacing, Hot Tin Plated

By Burndy  
Catalog # [YCA262NW](#)



Cu Compression terminal Designed for terminating Cu Conductors to switch pads, 2/0 Str., 1/2 IN Stud, 2 Pad holes, Hot tin plated

### Features

- Copper Compression Terminal designed for terminating copper conductors to switch pads
- 2/0 Str, 1/2" Stud, 2 Pad Holes
- Hot Tin Plated

### Specifications

|                                    |    |
|------------------------------------|----|
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Standards - RoHS Compliance Status | CM |
| Certification - cULus              | No |
| UL Listed                          | No |
| Certification - CSA Approved       | No |

### Conductor

|                             |         |
|-----------------------------|---------|
| Conductor - Copper Str Size | 2/0 AWG |
|-----------------------------|---------|

### Configuration

|                                                |          |
|------------------------------------------------|----------|
| Physical Attribute - Number of Crimps Required | 1        |
| Physical Attribute - Number of Holes           | 2        |
| Connector Type                                 | Terminal |

### Dimensions

|                                   |            |
|-----------------------------------|------------|
| Dimension - Pad Width inch        | 0.97 in    |
| Package Height                    | 0.000 in   |
| Dimension - Hole Size fraction    | 5/9        |
| Physical Attribute - Tongue Angle | Straight   |
| Dimension - B Length fraction     | 1-18/25 in |
| Package Weight                    | 0.000 lb.  |
| Package Length                    | 0.000 in   |

|                                   |            |
|-----------------------------------|------------|
| Package Width                     | 0.000 in   |
| Dimension - Z inch                | 0.62 in    |
| Dimension - L Length Overall mm   | 134 mm     |
| Dimension - B Length inch         | 1.72 in    |
| Dimension - Outside Diameter inch | 0.71 in    |
| Dimension - D inch                | 3.00 in    |
| Dimension - N inch                | 0.63 in    |
| Dimension - Hole Size mm          | 14 mm      |
| Dimension - Hole Size inch        | 0.56 in    |
| Dimension - Length Overall inch   | 5.27 in    |
| Dimension - Strip Length inch     | 1-13/16 in |
| Dimension - Stud Size inch        | 1/2        |

### General

|                           |                                                                     |
|---------------------------|---------------------------------------------------------------------|
| Plated                    | Y                                                                   |
| Trade Name                | HYLUG™                                                              |
| Die Index                 | <ul style="list-style-type: none"><li>• 166</li><li>• 206</li></ul> |
| UPC                       | 781810097236                                                        |
| Prefilled Oxide Inhibitor | N                                                                   |
| Material                  | Copper                                                              |
| Plating Type              | Tin - Hot Dipped                                                    |
| UPC 14 Digit GTIN         | 00781810097236                                                      |

### Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 4320 |
| Carton Quantity       | 15   |

### Product Assets

[Catalog \[English\]](#)