



YCA272NTN, Copper compression terminal, 2-Hole, 3/0 Str, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCA272NTN](#)

Cu Compression terminal, 3/0 str, .56"stud,5.33"L

Features

- Copper Compression Terminal Terminal
- 1/2" Stud, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	3/0 AWG
-----------------------------	---------

Configuration

Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.08 in
Dimension - Hole Size fraction	5/9
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-20/29 in
Dimension - Z inch	0.62 in
Dimension - L Length Overall mm	135 mm



Dimension - B Length inch	1.69 in
Dimension - Outside Diameter inch	0.79 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.33 in
Dimension - Strip Length inch	1 3/4
Dimension - Stud Size inch	1/2

General

Plated	Y
Trade Name	HYLUG™
Die Index	• 167 • 207 • 211
UPC	781810216033
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810216033

Logistics

Minimum Pack Quantity	6
Pallet Quantity	4608
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)