



YCA27R2N, Al compression lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing, 3/0

By Burndy
Catalog # [YCA27R2N](#)



AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 6.73 IN L

Features

- Aluminum Compression Terminal
- 2-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Size Range	3/0 (6/1) Pigeon AWG
Conductor - AL Str Size	3/0 AWG
Conductor - AL Str Size Range	3/0 AWG

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
Connector Type	Terminal

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in

Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.78 in
Dimension - L Length Overall mm	170 mm
Dimension - Pad Width inch	1.08 in
Package Height	0.000 in
Dimension - B Length inch	2.74 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - Length Overall inch	6.73 in

General

Die Index	247
Prefilled Oxide Inhibitor	Y
Plated	N
UPC 12 Digit	781810016657
UPC 14 Digit GTIN	00781810016657
Material	Aluminum
Plating Type	Unplated
UPC	781810016657

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	9800

Product Assets

[Catalog \[English\]](#)