



# YCA282NW, Copper Compression Terminal, 4/0 Str, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Hot Tin Plate

By Burndy  
Catalog # [YCA282NW](#)

Cu Compression terminal Designed for terminating Cu Conductors to switch pads, 4/0 Str., 1/2 IN Stud, 2 Pad holes, Hot tin plated

## Features

- Copper Compression Terminal Designed for Terminating Copper Conductors to Switch Pads
- 4/0 Str, 1/2" Stud, 2 Pad Holes
- Hot Tin Plated

## Specifications

|                                    |    |
|------------------------------------|----|
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Standards - RoHS Compliance Status | CM |
| Certification - cULus              | No |
| UL Listed                          | No |
| Certification - CSA Approved       | No |

## Conductor

|                                   |         |
|-----------------------------------|---------|
| Conductor - Copper Str Size Range | 4/0 AWG |
| Conductor - Copper Str Size       | 4/0 AWG |

## Configuration

|                                                |          |
|------------------------------------------------|----------|
| Physical Attribute - Number of Crimps Required | 1        |
| Physical Attribute - Number of Holes           | 2        |
| Connector Type                                 | Terminal |

## Dimensions

|                                   |          |
|-----------------------------------|----------|
| Dimension - Pad Width inch        | 1.22 in  |
| Dimension - Hole Size fraction    | 5/9      |
| Physical Attribute - Tongue Angle | Straight |



|                                   |             |
|-----------------------------------|-------------|
| Dimension - B Length fraction     | 1-69/100 in |
| Dimension - L Length Overall mm   | 136 mm      |
| Dimension - B Length inch         | 1.62 in     |
| Dimension - Outside Diameter inch | 0.89 in     |
| Dimension - N inch                | 0.63 in     |
| Dimension - Hole Size mm          | 14 mm       |
| Dimension - Hole Size inch        | 0.56 in     |
| Dimension - Length Overall inch   | 5.35 in     |
| Dimension - Strip Length inch     | 1 11/16     |
| Dimension - Stud Size inch        | 33/64       |

## General

|                           |                                                                     |
|---------------------------|---------------------------------------------------------------------|
| Plated                    | Y                                                                   |
| Trade Name                | HYLUG™                                                              |
| Die Index                 | <ul style="list-style-type: none"><li>• 168</li><li>• 208</li></ul> |
| Oxide Inhibitor Type      | Penetrox A                                                          |
| UPC                       | 781810087749                                                        |
| Prefilled Oxide Inhibitor | Y                                                                   |
| Material                  | Copper                                                              |
| Plating Type              | Tin - Hot Dipped                                                    |
| UPC 14 Digit GTIN         | 00781810087749                                                      |

## Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 2900 |
| Carton Quantity       | 25   |

## Product Assets

[Catalog \[English\]](#)