

YCA28RL2N, Al compression terminal, 2-Hole, 1/2" Stud, 1-3/4" Spacing, 4/0

By Burndy
Catalog # [YCA28RL2N](#)

Aluminum compression lug designed for terminating overhead conductors to switch pads and other substation switch yard apparatus,Die index:654



Features

- Aluminum Compression Terminal
- 2-Hole, 1/2" Stud, 1-3/4" Spacing

Application

Aluminum compression HYLUGs for terminating overhead conductors to switch pads and substation or switch yard apparatus.

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer
EU RoHS Indicator	No
Certification - UL Recognized	Contact Manufacturer
Buy America(n) Qualified	No
Certification - ETL	Contact Manufacturer
Standards - RoHS Compliance Status	No
Certification - CSA Approved	CM
UL Listed	No

Conductor

Conductor - ACSR Cmpt Size Range	4/0 AWG
Conductor - ACSR Str Size	4/0 (6/1) Penguin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penguin AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor Type	• ACSR C Str-Size • AAC

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
Connector Type	Terminal

Dimensions

Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	1.02 in
Dimension - L Length Overall mm	168 mm
Dimension - Pad Width inch	1.40 in
Package Height	0.000 in
Dimension - B Length inch	2.48 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - Length Overall inch	6.62 in

General

Die Index	654
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Sub Brand	HYLUG
Plated	N
Construction Material - Main Type	Aluminum
UPC 12 Digit	YCA-RL-2N
UPC 14 Digit GTIN	781810810484
Material	00781810810484
Plating Type	Aluminum
UPC	Unplated
	781810810484

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	5550

Product Assets

[Catalog \[English\]](#)