



YCA2C2N, Copper compression terminal,
2-hole pad, #2 AWG Str, 1/2" Stud, 1-3/4"
Spacing.

By Burndy
Catalog # [YCA2C2N](#)

Cu Compression terminal, 2 Holes, #2 (7) AWG STR, 1/2 IN Stud,
1.75 IN Spacing, 163 Index

Features

- Copper Compression Terminal
- 2-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Str Size	2 AWG

Configuration

Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.99 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/9
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-15/79 in
Package Weight	0.000 lb.



Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.62 in
Dimension - L Length Overall mm	123 mm
Dimension - B Length inch	1.19 in
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.83 in
Dimension - Strip Length inch	1 1/4

General

Plated	N
Trade Name	HYLUG™
Die Index	163
UPC	781810349915
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810349915

Logistics

Minimum Pack Quantity	1
Pallet Quantity	8700
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)