



YCA2C2NW, Copper Compression  
Terminal, #2 AWG, 2-Hole, 1/2" Stud, 1-3/4"  
Spacing, Hot Tin Plate

By Burndy  
Catalog # [YCA2C2NW](#)

Copper Compression Terminal; Copper Conductor to Switch  
Pads

Features

- Copper Compression Terminal
- 2-Hole, 1/2" Stud, 1-3/4" Spacing
- Hot Tin Plate

Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

Conductor

|                             |       |
|-----------------------------|-------|
| Conductor - Copper Str Size | 2 AWG |
| Range                       |       |
| Conductor - Copper Str Size | 2 AWG |

Configuration

|                                |          |
|--------------------------------|----------|
| Physical Attribute - Number of | 2        |
| Crimps Required                |          |
| Physical Attribute - Number of | 2        |
| Holes                          |          |
| Connector Type                 | Terminal |

Dimensions

|                                |          |
|--------------------------------|----------|
| Dimension - Pad Width inch     | 0.99 in  |
| Dimension - Hole Size fraction | 5/9      |
| Physical Attribute - Tongue    | Straight |
| Angle                          |          |



|                               |            |
|-------------------------------|------------|
| Dimension - B Length fraction | 1-15/79 in |
| Dimension - L Length Overall  | 123 mm     |
| mm                            |            |
| Dimension - B Length inch     | 1.19 in    |
| Dimension - Outside Diameter  | 0.5 in     |
| inch                          |            |
| Dimension - N inch            | 0.63 in    |
| Dimension - Hole Size mm      | 14 mm      |
| Dimension - Hole Size inch    | 0.56 in    |
| Dimension - Length Overall    | 4.83 in    |
| inch                          |            |
| Dimension - Strip Length inch | 1 1/4      |
| Dimension - Stud Size inch    | 1/2        |

General

|                           |                  |
|---------------------------|------------------|
| Plated                    | Y                |
| Trade Name                | HYLUG™           |
| Die Index                 | 163              |
| UPC                       | 781810349984     |
| Prefilled Oxide Inhibitor | N                |
| Material                  | Copper           |
| Plating Type              | Tin - Hot Dipped |
| UPC 14 Digit GTIN         | 00781810349984   |

Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 100  |
| Pallet Quantity       | 8700 |
| Carton Quantity       | 50   |

Product Assets

[Catalog \[English\]](#)