



YCA2R2N, Al compression terminal 2-Hole,
1/2" Stud, 1-3/4" Spacing, #2 AWG, ACSR,
AAC, AAAC

By Burndy
Catalog # [YCA2RL2N](#)

Al Comprsn terminal, #2 AWG ACSR(6-1, 7-1), AAC(7), AAAC(7)



Features

- Aluminum Compression Terminal
- 2-Hole, 1/2" Stud, 1-3/4" Spacing

Specifications

Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Cmpt Size Range	2 AWG
Conductor - ACSR Str Size	2 (6/1) Sparrow AWG 2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor Type	- ACSR C Str-Size - AAC

Configuration

Physical Attribute - Pad Configuration	2 Hole NEMA
Connector Type	Terminal

Dimensions

Package Length	0.000 in
----------------	----------

Dimension - E Spacing between Holes fraction	1-3/4
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.66
Dimension - L Length Overall mm	152
Dimension - Pad Width inch	0.91
Package Height	0.000 in
Dimension - B Length inch	2.20
Dimension - Bolt Hole Size inch	0.5
Dimension - Length Overall inch	6

General

Die Index	243 687 - BG
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Plated	N
UPC 12 Digit	781810810408
UPC 14 Digit GTIN	00781810810408
Material	Aluminum
Plating Type	Unplated
UPC	781810810408

Logistics

Minimum Pack Quantity	1
Carton Quantity	50
Pallet Quantity	12000

Product Assets

[Catalog \[English\]](#)